

# Push-in T-connector NPQM-T-Q14-E-P10

Part number: 570454

FESTO



## Data sheet

Feature	Value
Size	Standard
Nominal width	12 mm
Design	T-shape
Pack size	10
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.775 psi...232 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...70 °C
Product weight	77.1 g
Pneumatic connection 1	for pneumatic tubing outside diameter 14 mm
Pneumatic connection 2	for pneumatic tubing outside diameter 14 mm
Releasing ring color	Silver
Note on materials	RoHS-compliant
Housing material	Brass, nickel-plated
Material of tubing seal	NBR