

Electric linear actuator ELFR-...-35- -

Part number: 571435

FESTO



Data sheet

Feature	Value
Working stroke	50 mm...800 mm
Size	35
Mounting position	Any
Guide	Sliding guide Recirculating ball bearing guide
Structural design	Electric linear actuator without actuator
Max. acceleration	50 m/s ²
Max. speed	1 m/s...3 m/s
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP20
Ambient temperature	-10 °C...50 °C
2nd moment of area I _y	3770 mm ⁴
2nd moment of area I _z	4190 mm ⁴
Max. force F _y	50 N
Max. force F _z	50 N
Max. no-load resistance to shifting	3 N
Reference service life	5000 km
Additional moving mass per 10 mm stroke	0 g
Basic weight with 0 mm stroke	1200 g
Additional weight per 10 mm stroke	23 g
Profile material	Wrought aluminum alloy Anodized
Note on materials	RoHS-compliant
Drive cover material	Wrought aluminum alloy Anodized
Guide rail material	Steel
Slide material	Wrought aluminum alloy Anodized