

Cover plate VABB-L1-18

Part number: 574482



Data sheet

Feature	Value
Width dimension	19 mm
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Certification	RCM compliance mark c UL us - Recognized (OL)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Max. tightening torque for valve mounting	1.18 Nm
Product weight	50 g
Note on materials	RoHS-compliant
Cover plate material	Wrought aluminum alloy