

## Bus interface CDPX-F-CO

Part number: 575301

**FESTO**



## Data sheet

Feature	Value
Installation depth	24 mm
Height	91 mm
Length	41 mm
Certification	C-Tick c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...70 °C
Relative air humidity	5 - 85 % Non-condensing
Degree of protection	IP20
Ambient temperature	0 °C...50 °C
Product weight	150 g
Note on materials	RoHS-compliant
Fieldbus interface, type	CANopen
Fieldbus interface, connection technology	Plug Sub-D 9-pin
Fieldbus interface, transmission rate	9.6 kbit/s to 1 Mbit/s