


Connecting cable NEBV-C-S7WA44HS-K-5-N-LE36-S10

Part number: 577377

FESTO



Data sheet

Feature	Value
Based on norm	DIN 47100
Cable designation	Without label holder
Contact durability	50
Product weight	900 g
Electrical connection 1, function	Field device end
Electrical connection 1, design	Rectangular
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	44
Electrical connection 1, occupied pins/wires	36
Electrical connection 1, type of mounting	2x screw, 4-40 UNC With seal
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	36
DC operating voltage range	0 V...30 V
Current rating at 40° C	0.86 A
Protective earth connection	Not available
Cable length	5 m
Cable characteristic	Standard
Bending radius, fixed cable installation	39 mm
Bending radius, flexible cable installation	115 mm
Cable diameter	9.6 mm
Cable diameter tolerance	± 0.2 mm
Cable design	36 x 0.25 mm ²
Nominal conductor cross section	0.25 mm ²
Degree of protection	IP65 IP67 IP69K
Note on degree of protection	In mounted state

Feature	Value
Special features	Easy to clean
Ambient temperature	-5 °C...60 °C
Ambient temperature with flexible cable installation	-5 °C...60 °C
Storage temperature	-20 °C...40 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Contamination level	3
Corrosion resistance class (CRC)	3 - High corrosion stress
Material of cable sheath	PVC
Color cable sheath	Gray
Housing material	PA-reinforced
Housing colour	Gray
Material of screws	Stainless steel
Seals material	EPDM
Material of pin contacts	Bronze, gold-plated
Insulating sheath material	PVC