

**Sealing cap**  
**CV-PK-4-B**  
Part number: 6214

**FESTO**



**Data sheet**

| Feature                                  | Value                                                                                                  |
|------------------------------------------|--------------------------------------------------------------------------------------------------------|
| Pack size                                | 10                                                                                                     |
| Temperature-dependent operating pressure | -0.095 MPa...1 MPa<br>-0.95 bar...10 bar<br>-13.775 psi...145 psi                                      |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7::-]                                                           |
| LABS (PWIS) conformity                   | VDMA24364-B2-L                                                                                         |
| Ambient temperature                      | -10 °C...80 °C                                                                                         |
| Pneumatic connection 1                   | For pneumatic tubing outside diameter 6 mm<br>For barbed fitting, inside diameter 4 mm, with union nut |
| Note on materials                        | RoHS-compliant                                                                                         |
| Cap material                             | TPE-U(PU)                                                                                              |