

Sealing cap
CV-PK-6-B
Part number: 6215



Data sheet

Feature	Value
Pack size	10
Temperature-dependent operating pressure	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...80 °C
Pneumatic connection 1	for pneumatic tubing outside diameter 8 mm For barbed fitting, inside diameter 6 mm, with union nut
Note on materials	RoHS-compliant
Cap material	TPE-U(PU)