


OR gate OS-1/4-B

Part number: 6682

FESTO



Data sheet

Feature	Value
Valve function	OR function
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Type of mounting	With through-hole
Standard nominal flow rate	1170 l/min
Operating pressure	1 bar...10 bar
Ambient temperature	-10 °C...60 °C
Housing material	Wrought aluminum alloy
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::]
Nominal width	6.5 mm
Mounting position	Any
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C...60 °C
Product weight	110 g
Pneumatic connection 3	G1/4
Note on materials	RoHS-compliant
Seals material	NBR