

**Connection block**  
**VABM-B10-25E-N12-9-P3**  
Part number: 8026295

**FESTO**



**Data sheet**

| Feature                          | Value                         |
|----------------------------------|-------------------------------|
| Width dimension                  | 27.5 mm                       |
| Mounting position                | Any                           |
| Max. no. of valve positions      | 9                             |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity           | VDMA24364-B1/B2-L             |
| Product weight                   | 2364 g                        |
| Type of mounting                 | With through-hole             |
| Pilot air port 12                | 1/8 NPT                       |
| Pneumatic connection 1           | 1/2 NPT                       |
| Pneumatic connection 3           | 1/2 NPT                       |
| Note on materials                | RoHS-compliant                |
| Manifold rail material           | Wrought aluminum alloy        |