

Solenoid coil VACN-N-K1-3A-EX4-M

Part number: 8029141

FESTO



Data sheet

Feature	Value
Actuation type	Electrical
Mounting position	Any
Duty cycle	100%
Insulation class	F
Enameled wire insulation class	H
Coil characteristics	230 V AC: 50/60 Hz, power 2.1 VA
Permissible voltage fluctuations	+/- 10 %
Maritime classification	See certificate
CE marking (see declaration of conformity)	as per EU explosion protection directive (ATEX) As per EU RoHS directive
UKCA marking (see declaration of conformity)	acc. to UK EX instructions To UK RoHS instructions
Explosion protection certification outside the EU	EPL Db (BR) EPL Db (CN) EPL Db (GB) EPL Db (IEC-EX) EPL Gb (BR) EPL Gb (CN) EPL Gb (GB) EPL Gb (IEC-EX)
Explosion prevention and protection	Zone 1 (ATEX) Zone 1 (BR) Zone 1 (CN) Zone 1 (IEC-EX) Zone 1 (UKEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 21 (BR) Zone 21 (CN) Zone 21 (IEC-EX) Zone 21 (UKEX) Zone 22 (ATEX)
Certificate issuing authority	CCC 2021322307003994 DNV 15.0189X DNV TAA000011J GYJ21.1327X IECEX PTB 15.0016X PTB 14 ATEX 2027 X

Feature	Value
ATEX category gas	II 2G
ATEX category for dust	II 2D
Type of ignition protection for gas	Ex mb IIC T6 Gb
Type of (ignition) protection for dust	Ex mb IIIC T80°C Db
Explosive ambient temperature	-20°C ≤ Ta ≤ +50°C
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP65
Ambient temperature	-20 °C...50 °C
Product weight	353 g
Electrical connection	Cable
Cable diameter	7 mm
Cable length	3 m
Type of mounting	With knurled nut
Note on materials	RoHS-compliant
Housing material	Polymer Steel
Material of winding	Copper