

Duct separation VABD-S1-1-P2-C

Part number: 8029439

FESTO



Data sheet

Feature	Value
Based on norm	ISO 5599-1
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Suitability for vacuum	yes
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C...60 °C
Temperature of medium	-10 °C...50 °C
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Ambient temperature	-10 °C...50 °C
Product weight	70 g
Note on materials	RoHS-compliant
Separator plate material	Steel NBR