

**T-fitting**  
**NPFC-T-G12-2R12-FMM**  
Part number: 8030258



**Data sheet**

| Feature                          | Value                                         |
|----------------------------------|-----------------------------------------------|
| Threaded fitting material        | Brass, nickel-plated                          |
| Pack size                        | 10                                            |
| Operating pressure               | -0.95 bar...50 bar                            |
| Operating medium                 | Compressed air as per ISO 8573-1:2010 [:-::-] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress                      |
| LABS (PWIS) conformity           | VDMA24364-B1/B2-L                             |
| Ambient temperature              | -20 °C...150 °C                               |
| Product weight                   | 100.7 g                                       |
| Pneumatic connection 1           | G1/2                                          |
| Pneumatic connection 2           | R1/2                                          |
| Note on materials                | RoHS-compliant                                |