

**Sub-base**  
**VMPA1-FB-AP-4-1-T1-RV**  
Part number: 8034549



**Data sheet**

| Feature                          | Value                                         |
|----------------------------------|-----------------------------------------------|
| Width                            | 49 mm                                         |
| Length                           | 107.3 mm                                      |
| Width dimension                  | 10.5 mm                                       |
| Max. no. of valve positions      | 4                                             |
| Operating pressure               | -0.09 MPa...1 MPa<br>-0.9 bar...10 bar        |
| Pilot pressure MPa               | 0.3 MPa...0.8 MPa                             |
| Pilot pressure                   | 3 bar...8 bar                                 |
| Operating medium                 | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Corrosion resistance class (CRC) | 0 - No corrosion stress                       |
| LABS (PWIS) conformity           | VDMA24364-B1/B2-L                             |
| Ambient temperature              | -5 °C...50 °C                                 |
| Product weight                   | 190 g                                         |
| Note on materials                | RoHS-compliant                                |
| Material of sub-base             | Die-cast aluminum                             |