


Sub-base VMPAL-AP-14-T1-RV

Part number: 8034558

FESTO



Data sheet

| Feature | Value |
|--|--|
| Width | 14 mm 14.9 mm |
| Length | 107.3 mm |
| Width dimension | 14.9 mm |
| Pressure zone separation | Channel 1 |
| Integrated function | Non-return valve |
| Max. no. of valve positions | 1 |
| Flow direction | Non-reversible |
| Valve manifold design | Valve sizes can be mixed |
| Operating pressure | -0.09 MPa...1 MPa -0.9 bar...10 bar |
| Pilot pressure MPa | 0.3 MPa...0.8 MPa |
| Pilot pressure | 3 bar...8 bar |
| Suitability for vacuum | no |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -5 °C...50 °C |
| Product weight | 35 g |
| Pneumatic connection 2 | for 14 mm cartridge |
| Pneumatic connection 4 | For 14 mm cartridge |
| Note on materials | RoHS-compliant |
| Material of sub-base | PA-reinforced |