


Sub-base VMPAL-AP-20-RV

Part number: 8034561

FESTO



Data sheet

Feature	Value
Width	20 mm 21.2 mm
Length	107.3 mm
Width dimension	21.2 mm
Integrated function	Non-return valve
Max. no. of valve positions	1
Flow direction	Non-reversible
Valve manifold design	Valve sizes can be mixed
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Pilot pressure MPa	0.3 MPa...0.8 MPa
Pilot pressure	3 bar...8 bar
Suitability for vacuum	no
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C...50 °C
Product weight	50 g
Pneumatic connection 2	for 18 mm cartridge
Pneumatic connection 4	For 18 mm cartridge
Note on materials	RoHS-compliant
Material of sub-base	PA-reinforced