

Plastic tubing PAN-R-22X2-SW

Part number: 8036207

FESTO



Data sheet

Feature	Value
Outside diameter	22 mm
Bending radius relevant for flow rate	350 mm
Inside diameter	18 mm
Operating pressure for entire temperature range	-0.095 MPa...0.8 MPa -0.95 bar...8 bar -13.775 psi...116 psi
Temperature-dependent operating pressure	-0.095 MPa...1.4 MPa -0.95 bar...14 bar -13.775 psi...203 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C...80 °C
Product weight by length	0.131 kg/m
Pneumatic connection	For plug connection outside diameter 22 mm
Color	Black
Shore hardness	D 62 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	TPE-A