

Supply plate VABF-S1-1-P1A12-N12

Part number: 8037654

FESTO



Data sheet

| Feature | Value |
|--------------------------------------------|--------------------------------------------------------------------|
| Width | 44 mm |
| Exhaust air function | Via throttle plate |
| Based on norm | ISO 5599-1 |
| Max. no. of valve positions | 1 |
| Operating pressure | 0 MPa...1 MPa 0 bar...10 bar |
| Suitability for vacuum | yes |
| CE marking (see declaration of conformity) | As per EU low voltage directive |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 °C...60 °C |
| Temperature of medium | -10 °C...50 °C |
| Pilot medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -10 °C...50 °C |
| Product weight | 650 g |
| Pneumatic connection 1 | 1/2 NPT |
| Pneumatic connection 3 | 1/2 NPT |
| Pneumatic connection 5 | 1/2 NPT |
| Exhaust plate material | PA |
| Note on materials | RoHS-compliant |
| Supply plate material | Die-cast aluminum |