



Regulator plate VMPA14-B8-R2C2-C-10

Part number: 8043340

FESTO



Data sheet

Feature	Value
Width	14 mm
Mounting position	Any
Pneumatic vertical stacking	Pressure regulator for 2
Controller function	Outlet pressure constant With secondary exhausting
Optional pressure gauge	Possible
Pressure regulation range	2 bar...6 bar
Inlet pressure 1	0.5 bar...10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 as per IEC 60529
Ambient temperature	-5 °C...50 °C
Max. tightening torque	0.65 Nm
Product weight	76 g
Vertical stacking mounting type	On manifold sub-base
Pressure gauge connection	M5
Note on materials	RoHS-compliant
Material of operator panel	PA
Seals material	NBR
Controller housing material	PA