

Fixed flow restrictor VFFG-T-F6-10

Part number: 8047355

FESTO



Data sheet

Feature	Value
Valve function	Flow control function
Type of mounting	Tapped
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Ambient temperature	-5 °C...60 °C
Certification	c UL us - Recognized (OL)
Size	For 5.8 mm diameter
Nominal width	1.05 mm
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Product weight	1.2 g
Note on materials	RoHS-compliant