

# Non return valve VABF-L1-10H-H2

Part number: 8047364

FESTO



## Data sheet

| Feature                                  | Value                                                              |
|------------------------------------------|--------------------------------------------------------------------|
| Valve size                               | 10 mm                                                              |
| Valve function                           | Unlockable non-return function                                     |
| Operating pressure                       | 0.05 MPa...0.8 MPa<br>0.5 bar...8 bar                              |
| Certification                            | c UL us - Recognized (OL)                                          |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 1 - Low corrosion stress                                           |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L                                                  |
| Ambient temperature                      | -5 °C...60 °C                                                      |
| Product weight                           | 0.4 g                                                              |
| Type of mounting                         | Tapped                                                             |
| Note on materials                        | RoHS-compliant                                                     |