

Parallel kit
EAMM-U-70-D40-60RA-96
Part number: 8058952



Data sheet

Feature	Value
Size	70
Mounting position	Any
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	118 kgmm ²
No-load driving torque	0.18 Nm
Transferable torque	7 Nm
Product weight	1800 g
Interface code, actuator	D40
Interface code, motor in	60RA
Note on materials	RoHS-compliant