


Parallel kit
EAMM-U-86-S62-60PA-102
Part number: 8059026

FESTO



Data sheet

Feature	Value
Size	86
Mounting position	Any
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	175 kgmm ²
No-load driving torque	0.25 Nm
Transferable torque	9.5 Nm
Product weight	2500 g
Interface code, actuator	S62
Interface code, motor in	60PA
Note on materials	RoHS-compliant