

# Quick coupling plug NPHS-S6-M-G14F

Part number: 8059262

FESTO



## Data sheet

| Feature                                              | Value                                                               |
|------------------------------------------------------|---------------------------------------------------------------------|
| Nominal width                                        | 7.85 mm                                                             |
| Operating pressure for entire temperature range      | -0.095 MPa...1.2 MPa<br>-0.95 bar...12 bar<br>-13.775 psi...174 psi |
| Standard nominal flow rate                           | 1002 l/min...1950 l/min                                             |
| Nominal flow rate standardized according to ISO 8778 | 1086.2 l/min...2113.8 l/min                                         |
| Operating medium                                     | Compressed air as per ISO 8573-1:2010 [7:::]                        |
| Information on operating and pilot media             | Operation with oil lubrication possible                             |
| Corrosion resistance class (CRC)                     | 1 - Low corrosion stress                                            |
| LABS (PWIS) conformity                               | VDMA24364-B1/B2-L                                                   |
| Ambient temperature                                  | -10 °C...60 °C                                                      |
| Product weight                                       | 28 g                                                                |
| Pneumatic connection 1                               | Internal thread G1/4                                                |
| Note on materials                                    | RoHS-compliant                                                      |
| Information on materials                             | Steel, galvanized                                                   |