

Quick coupling plug NPHS-S6-M-G12F

Part number: 8059264

FESTO



Data sheet

Feature	Value
Nominal width	7.85 mm
Operating pressure for entire temperature range	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Standard nominal flow rate	1038 l/min...2050 l/min
Nominal flow rate standardized according to ISO 8778	1125.2 l/min...2222.2 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Product weight	49 g
Pneumatic connection 1	Internal thread G1/2
Note on materials	RoHS-compliant
Information on materials	Steel, galvanized