


Axial kit
EAMM-A-M80-90GB
Part number: 8063567



Data sheet

Feature	Value
Nominal length	27 mm
Mounting position	Any
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	151 kgmm ²
Transferable torque	60 Nm
Product weight	1279 g
Interface code, actuator	M80
Interface code, motor in	90GB
Note on materials	RoHS-compliant