

Electronics module

VMPA14-MPM-EMM-4

Part number: 8066768



Data sheet

Feature	Value
Max. no. of valve positions	4
Max. no. of solenoid coils	4
Nominal pick-up current per solenoid coil	80 mA to 25 ms
Nominal current with current reduction	25 mA after 25 ms
Corrosion resistance class (CRC)	1 - Low corrosion stress (when installed)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	30 g
Housing material	POM
Note on materials	RoHS-compliant