


Double nipple NPFC-D-G12-G34-M

Part number: 8069216

FESTO



Data sheet

Feature	Value
Threaded fitting material	Brass, nickel-plated
Pack size	10
Operating pressure	-0.95 bar...50 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [:-::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...150 °C
Product weight	58.7 g
Pneumatic connection 1	G1/2
Pneumatic connection 2	G3/4
Note on materials	RoHS-compliant