



Holding brake DACS-40-A-R3-S

Part number: 807 2777

FESTO



Data sheet

Feature	Value
Mounting position	Any
Clamping type with active direction	Both sides Clamped by spring, released by compressed air
Position sensing	For proximity sensor
Safety function	Holding and stopping a movement
Performance Level (PL)	Stopping, holding, blocking of movement/Category 1, Performance Level c
Operating pressure	0.38 MPa...0.8 MPa 3.8 bar...8 bar 55.1 psi...116 psi
Max. permissible test pressure	8 bar
Min. release pressure	3.8 bar
Round material to be clamped	40 mm
Certification	German Technical Control Board (TÜV)
CE marking (see declaration of conformity)	as per EU machinery directive
UKCA marking (see declaration of conformity)	To UK instructions for machines
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Certificate issuing authority	TÜV CA 697
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C...80 °C
Static holding force	17000 N
Product weight	34500 g
Type of mounting	With internal thread With accessories
Clamping unit release connection	G3/8
Note on materials	RoHS-compliant

Feature	Value
Seals material	NBR TPE-U(PU)
Material of spring	High-alloy steel
Housing material	Steel
Clamping jaws material	Tool steel
Material of piston	Steel