

Pneumatic shock absorber DYEF-G8-M5-Y1

Part number: 8073903

FESTO



Data sheet

Feature	Value
Size	M5
Stroke	1.5 mm
Cushioning	Elastic cushioning rings/pads at both ends, without fixed metal stop
Mounting position	Any
Position sensing	None
Max. impact velocity	0.8 m/s
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Cushioning length	1.5 mm
Max. tightening torque	0.8 Nm
Max. energy absorption per stroke	0.05 J
Product weight	8.4 g
Type of mounting	With threaded sleeve
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	High-alloy steel