

Adapter kit
DHAA-G-R3-25-B19-32
Part number: 8079196



Data sheet

Feature	Value
Size	25
Mounting position	Any
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...50 °C
Product weight	65 g
Type of mounting	With internal thread
Adapter plate material	Wrought aluminum alloy, anodized
Material of screws	Steel, galvanized