

Pressure gauge
PAGN-63-16-G14-R1-1.6-0.5-V2
 Part number: 8081401

FESTO



Data sheet

Feature	Value
Display range	0 bar...16 bar
Conforms to standard	EN 837-1
Pressure gauge nominal size	63
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Structural design	Bourdon tube pressure gauge
Type of mounting	Line installation
Operating medium	Inert gas Neutral liquids
Information on operating and pilot media	No acetylene No oxygen
Operating pressure	0 MPa...1.6 MPa 0 bar...16 bar 0 psi...232 psi
Intermittent load factor	0.66
Measurement accuracy class	1.6
Degree of protection	IP65
Storage temperature	-40 °C...70 °C
Temperature of medium	-40 °C...200 °C
Ambient temperature	-40 °C...60 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Connection position	Centered on rear side
Pneumatic connection	G1/4
Materials in contact with the media	High-alloy stainless steel
Material of screwed plug	High-alloy stainless steel
Housing material	ABS High-alloy stainless steel
Inspection window material	PC

Feature	Value
Housing colour	Silver
Product weight	160 g
Scale	Double scale bar (außen) psi (internal)