

Quick coupling
EAMD-32-32-14-16X20-U
Part number: 8086051



Data sheet

Feature	Value
Diameter of holder 1	14 mm
Diameter of holder 2	16 mm
Size	32
Nominal length	32 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	14.5 kgmm ²
Transferable torque	16 Nm
Product weight	124 g
Note on materials	RoHS-compliant