


On/off valve MS4-EE-1/4-V24-B

Part number: 8091771

FESTO



Data sheet

Feature	Value
Series	MS
Size	4
Width dimension	40 mm
Structural design	Poppet valve, electrically actuated
Actuation type	Electrical
Manual override	Detenting Non-detenting
Reset method	Mechanical spring
Type of control	Pilot-controlled
Valve function	3/2, closed, monostable
Operating pressure	0.3 MPa...0.7 MPa 3 bar...7 bar
Lap	Underlap
C value	8.36 l/sbar
b-value	0.49
Standard nominal flow rate	2000 l/min
Standard flow rate exhaust 6-> 0 bar	1600 l/min
Coil characteristics	24 V DC: 2.3 W
Permissible voltage fluctuations	+/- 10 %
On time	29 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 7 according to ISO 14644-1
Temperature of medium	-5 °C...50 °C
Degree of protection	IP65
Ambient temperature	-5 °C...50 °C
Type of mounting	With wall/surface bracket
Mounting position	Any
Switching position indication	with accessories

Feature	Value
Product weight	194 g
Pneumatic connection 1	G1/4
Pneumatic connection 2	G ¹ / ₄
Pneumatic connection 3	G1/4
Pilot air supply port	Internal
Electrical connection	Form C as per EN 175301-803
Signal status display	With accessories
Selection of additional function	with muffler
Seals material	HNBR NBR
Housing material	PA-reinforced