

Position indicator SAMH-F12-MK

Part number: 8092711

FESTO



Data sheet

Feature	Value
Mounting position	Any
Structural design	Without sensors
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Application note	In case of use with angle seat valve VZXA, the SIL license on the overall product is invalidated.
Note on materials	RoHS-compliant
Ambient temperature	-20 °C...60 °C
Storage temperature	-10 °C...60 °C
Product weight	118 g
Seals material	EPDM
Housing material	Aluminum PA-reinforced
Degree of protection	IP65 IP67
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III