

**Service unit**  
**MS4-EM1FR-1/4-D6-C-P-VC-AG-BAR-WPE-B**  
Part number: 8098372

**FESTO**



**Data sheet**

| Feature                                  | Value                                                                         |
|------------------------------------------|-------------------------------------------------------------------------------|
| Size                                     | 4                                                                             |
| Series                                   | MS                                                                            |
| Mounting position                        | Vertical +/- 5°                                                               |
| Pressure gauge                           | with pressure gauge                                                           |
| Operating pressure                       | 0.1 MPa...1 MPa<br>1 bar...10 bar<br>14.5 psi...145 psi                       |
| Standard flow rate exhaust 6-> 0 bar     | 1400 l/min                                                                    |
| Standard nominal flow rate               | 1500 l/min                                                                    |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                                 |
| Information on operating and pilot media | Compatibility with ester oil not given                                        |
| Corrosion resistance class (CRC)         | 1 - Low corrosion stress                                                      |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L                                                             |
| Storage temperature                      | -5 °C...50 °C                                                                 |
| Temperature of medium                    | 5 °C...50 °C                                                                  |
| Ambient temperature                      | 5 °C...50 °C                                                                  |
| Product weight                           | 470 g                                                                         |
| Type of mounting                         | Line installation<br>With mounting bracket<br>With accessories<br>Optionally: |
| Note on materials                        | RoHS-compliant                                                                |