

**Service unit**  
**MS4-EM1FR-1/4-D6-C-P-M-AG-BAR-WPE-B**  
Part number: 8098373

**FESTO**



**Data sheet**

| Feature                                           | Value                                                                         |
|---------------------------------------------------|-------------------------------------------------------------------------------|
| Size                                              | 4                                                                             |
| Series                                            | MS                                                                            |
| Mounting position                                 | Vertical +/- 5°                                                               |
| Pressure gauge                                    | with pressure gauge                                                           |
| Operating pressure                                | 0.1 MPa...1 MPa<br>1 bar...10 bar<br>14.5 psi...145 psi                       |
| Standard flow rate exhaust 6-> 0 bar              | 1400 l/min                                                                    |
| Normal nominal flow rate (normalized to DIN 1343) | 1500 l/min                                                                    |
| Operating medium                                  | Compressed air as per ISO 8573-1:2010 [7:4:4]                                 |
| Information on operating and pilot media          | Compatibility with ester oil not given                                        |
| Corrosion resistance class (CRC)                  | 1 - Low corrosion stress                                                      |
| LABS (PWIS) conformity                            | VDMA24364-B1/B2-L                                                             |
| Storage temperature                               | -5 °C...50 °C                                                                 |
| Temperature of medium                             | -5 °C...50 °C                                                                 |
| Ambient temperature                               | -5 °C...50 °C                                                                 |
| Product weight                                    | 470 g                                                                         |
| Type of mounting                                  | Optionally:<br>Line installation<br>With mounting bracket<br>With accessories |
| Note on materials                                 | RoHS-compliant                                                                |