

Connector plate VABS-B14-T-FG14

Part number: 8098884

FESTO



Data sheet

Feature	Value
Mounting position	Any
Structural design	Connection direction upward
Operating pressure	1.5 bar...10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...60 °C
Temperature of medium	-20 °C...60 °C
Ambient temperature	-20 °C...60 °C
Product weight	192 g
Type of mounting	With through-hole
Pneumatic connection 2	Flange 1/4 with NAMUR port pattern G1/4
Pneumatic connection 4	Flange 1/4 with NAMUR port pattern G1/4
Note on materials	RoHS-compliant
Material of sub-base	Wrought aluminum alloy