


Axial kit
EAMM-A-V32-58AA
Part number: 8098982



Data sheet

Feature	Value
Nominal length	41 mm
Mounting position	Any
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	1.03 kgmm ²
Transferable torque	1.5 Nm
Product weight	192 g
Interface code, actuator	V32
Interface code, motor in	58AA
Note on materials	RoHS-compliant