

# Quick coupling EAMC-56-58-22-25

Part number: 8099431

FESTO



## Data sheet

| Feature                | Value                 |
|------------------------|-----------------------|
| Diameter of holder 1   | 22 mm                 |
| Diameter of holder 2   | 25 mm                 |
| Size                   | 56                    |
| Nominal length         | 58 mm                 |
| Mounting position      | Any                   |
| Max. rotational speed  | 5500 rpm              |
| LABS (PWIS) conformity | VDMA24364-B2-L        |
| Storage temperature    | -25 °C...60 °C        |
| Relative air humidity  | 0 - 95 %              |
| Ambient temperature    | -25 °C...60 °C        |
| Mass moment of inertia | 128 kgmm <sup>2</sup> |
| Transferable torque    | 60 Nm                 |
| Product weight         | 272 g                 |
| Note on materials      | RoHS-compliant        |