

# Exhaust plate VABF-B14-M3-N14

Part number: 8099627

**FESTO**



## Data sheet

| Feature                          | Value                                         |
|----------------------------------|-----------------------------------------------|
| Mounting position                | Any                                           |
| Operating pressure               | 1.5 bar...10 bar                              |
| Operating medium                 | Compressed air as per ISO 8573-1:2010 [7::-]  |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress                 |
| LABS (PWIS) conformity           | VDMA24364 zone III                            |
| Storage temperature              | -20 °C...80 °C                                |
| Temperature of medium            | -20 °C...80 °C                                |
| Ambient temperature              | -20 °C...80 °C                                |
| Product weight                   | 280.5 g                                       |
| Type of mounting                 | With through-hole                             |
| Pneumatic connection 1           | 1/4 NPT                                       |
| Pneumatic connection 2           | Flange 1/4 with NAMUR port pattern            |
| Pneumatic connection 4           | Flange 1/4 with NAMUR port pattern<br>1/4 NPT |
| Note on materials                | RoHS-compliant                                |
| Controller housing material      | Wrought aluminum alloy                        |