

**Axial kit**  
**EAMM-A-P8-38A-70AA**  
Part number: 8105920



**Data sheet**

| Feature                  | Value          |
|--------------------------|----------------|
| Mounting position        | Any            |
| LABS (PWIS) conformity   | VDMA24364-B2-L |
| Storage temperature      | -25 °C...60 °C |
| Relative air humidity    | 0 - 95 %       |
| Degree of protection     | IP40           |
| Ambient temperature      | -10 °C...60 °C |
| Transferable torque      | 12.5 Nm        |
| Product weight           | 203 g          |
| Interface code, actuator | P8-38A         |
| Interface code, motor in | 70AA<br>70AB   |
| Note on materials        | RoHS-compliant |