

Proximity sensors

SDBF-FAS-1L-PU-K-9-N-LE

Part number: 8106571

FESTO



Data sheet

Feature	Value
Design	for round slot
Note on materials	RoHS-compliant
Measured variable	Position
Measuring principle	Magneto-resistive
Ambient temperature	-4 °F...176 °F
Switching output	PNP
Switching element function	N/O contact
On time	4 µs
Max. output current	200 mA
Max. switching capacity DC	4.8 W
Voltage drop	1 V
Short-circuit protection	yes
DC operating voltage range	6 V...24 V
Reverse polarity protection	yes
Electrical connection 1, connection type	Cable
Electrical connection 1, connection technology	Open end
Electrical connection 1, number of pins/wires	3
Connection outlet orientation	Longitudinal
Color cable sheath	Black
Material of cable sheath	PVC
Type of mounting	Screwed tightly Can be inserted in slot lengthwise
Mounting position	Any
Housing colour	Transparent
Switching status indication	LED
Ambient temperature with flexible cable installation	-20 °C...80 °C
Degree of protection	NEMA 6
LABS (PWIS) conformity	VDMA24364 zone III