


Shock absorber DYSS-G8-4-4-Y1F-G2

Part number: 8111384

FESTO



Data sheet

Feature	Value
Size	4
Stroke	4 mm
Cushioning	Self-adjusting
Mounting position	Any
Position sensing	None
Max. impact velocity	1 m/s
Reset time at room temperature	0.2 s
Reset time at min. ambient temperature	1 s
Mode of operation	Pushing Single-acting
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...80 °C
Cushioning length	4 mm
Max. stop force	100 N
Max. tightening torque	1 Nm
Max. energy absorption per stroke	0.8 J
Max. energy absorption per hour	5500 J
Max. residual energy	0.006 J
Resetting force	0.7 N
Min. insertion force	4.5 N
Product weight	10.2 g
Load range	1.7 kg
Type of mounting	With threaded sleeve
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	High-alloy steel
Piston rod material	High-alloy steel