

Push-in L-fitting NPQE-L-R38-Q8-P5

Part number: 8112953

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Standard |
| Nominal width | 6 mm |
| Type of seal on screwed plug | Coating |
| Mounting position | Any |
| Design | L-shape |
| Pack size | 5 |
| Structural design | Push-pull principle |
| Operating pressure for entire temperature range | -0.095 MPa...0.8 MPa -0.95 bar...8 bar -13.775 psi...116 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Cleanroom class | Class 4 according to ISO 14644-1 |
| Ambient temperature | -5 °C...60 °C |
| Product weight | 22.44 g |
| Type of mounting | External hexagon, AF 17 |
| Pneumatic connection 1 | External thread R3/8 |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 8 mm |
| Releasing ring color | Blue |
| Note on materials | RoHS-compliant |
| Housing material | Brass, nickel-plated PBT |
| Material of threaded seal | PTFE |
| Releasing ring material | POM |
| Material of tubing seal | NBR |
| Material of tube retaining claw | Stainless steel |