

# Push-in T-connector NPQE-T-Q16-E-P5

Part number: 8113154

FESTO



## Data sheet

Feature	Value
Size	Standard
Nominal width	14.3 mm
Mounting position	Any
Design	T-shape
Pack size	5
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.095 MPa...0.8 MPa -0.95 bar...8 bar -13.775 psi...116 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Cleanroom class	Class 4 according to ISO 14644-1
Ambient temperature	-5 °C...60 °C
Product weight	37.85 g
Pneumatic connection 1	for pneumatic tubing outside diameter 16 mm
Pneumatic connection 2	for pneumatic tubing outside diameter 16 mm
Releasing ring color	Blue
Note on materials	RoHS-compliant
Housing material	PBT
Releasing ring material	POM
Material of tubing seal	NBR
Material of tube retaining claw	Stainless steel