

Safety clip
NPAP-QE-S-Q10-P10
Part number: 8113231

FESTO



Data sheet

Feature	Value
Pack size	10
Mounting position	Any
Operating pressure for entire temperature range	-0.095 MPa...0.8 MPa -0.95 bar...8 bar -13.775 psi...116 psi
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Cleanroom class	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
Ambient temperature	-5 °C...60 °C
Product weight	0.23 g
Pneumatic connection	For pneumatic tubing outside diameter 10 mm
Note on materials	RoHS-compliant