

**Safety clip**  
**NPAP-QE-S-Q16-P10**  
Part number: 8113233

**FESTO**



**Data sheet**

| Feature                                         | Value                                                                                    |
|-------------------------------------------------|------------------------------------------------------------------------------------------|
| Pack size                                       | 10                                                                                       |
| Mounting position                               | Any                                                                                      |
| Operating pressure for entire temperature range | -0.095 MPa...0.8 MPa<br>-0.95 bar...8 bar<br>-13.775 psi...116 psi                       |
| Corrosion resistance class (CRC)                | 1 - Low corrosion stress                                                                 |
| LABS (PWIS) conformity                          | VDMA24364 zone III                                                                       |
| Cleanroom class                                 | Statically installed element, no meaningful evaluation possible according to ISO 14644-1 |
| Ambient temperature                             | -5 °C...60 °C                                                                            |
| Product weight                                  | 0.39 g                                                                                   |
| Pneumatic connection                            | For tubing O.D. 16 mm                                                                    |
| Note on materials                               | RoHS-compliant                                                                           |