

Manifold block

VABM-C12-6M-M5-M3-10

Part number: 8122794

FESTO



Data sheet

| Feature | Value |
|--|---|
| Width | 20 mm |
| Mounting position | Any |
| Structural design | Connection direction downwards |
| Max. no. of valve positions | 10 |
| Operating pressure | -0.1 MPa...0.7 MPa -1 bar...7 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [6:4:1] |
| Information on operating and pilot media | Maximum particle size 5 µm |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Ambient temperature | 5 °C...50 °C |
| Product weight | 49.5 g |
| Type of mounting | With through-hole |
| Pneumatic connection 1 | M5 |
| Pneumatic connection 2 | M3 |
| Pneumatic connection 3 | M5 |
| Note on materials | RoHS-compliant |
| Manifold rail material | Wrought aluminum alloy |