

Retainer VMPA14-FTI

Part number: 8129127

FESTO



Data sheet

Feature	Value
Size	14
Mounting position	Any
Pack size	10
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar -13.05 psi...145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C...40 °C
Temperature of medium	-5 °C...60 °C
Ambient temperature	-5 °C...60 °C
Product weight	0.1 g
Type of mounting	Clamped
Note on materials	RoHS-compliant
Retainer bracket material	POM