

Flow control -SET VMPA14-FT-NW0.3-1.7

Part number: 8129129

FESTO



Data sheet

Feature	Value
Valve function	Flow control function
Pneumatic connection 1	Sub-base
Type of mounting	Clamped
Standard nominal flow rate in flow control direction	3.5 l/min...115 l/min
Operating pressure	-0.09 bar...1 bar -0.09 bar...1 bar
Ambient temperature	-5 °C...60 °C
Size	14
Nominal width	0.3 mm...1.7 mm
Mounting position	Any
Pack size	2
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C...40 °C
Temperature of medium	-5 °C...60 °C
Product weight	0.6 g
Note on materials	RoHS-compliant
Retainer bracket material	POM
Hollow bolt material	Wrought aluminum alloy